

220mm

EN ES FR NL DA NO AR JP

GB IT PL SV SE TR CH TH RU

CE, EN ISO 22716, EN ISO 22717, EN ISO 22718, EN ISO 22719, EN ISO 22720, EN ISO 22721, EN ISO 22722, EN ISO 22723, EN ISO 22724, EN ISO 22725, EN ISO 22726, EN ISO 22727, EN ISO 22728, EN ISO 22729, EN ISO 22730, EN ISO 22731, EN ISO 22732, EN ISO 22733, EN ISO 22734, EN ISO 22735, EN ISO 22736, EN ISO 22737, EN ISO 22738, EN ISO 22739, EN ISO 22740, EN ISO 22741, EN ISO 22742, EN ISO 22743, EN ISO 22744, EN ISO 22745, EN ISO 22746, EN ISO 22747, EN ISO 22748, EN ISO 22749, EN ISO 22750, EN ISO 22751, EN ISO 22752, EN ISO 22753, EN ISO 22754, EN ISO 22755, EN ISO 22756, EN ISO 22757, EN ISO 22758, EN ISO 22759, EN ISO 22760, EN ISO 22761, EN ISO 22762, EN ISO 22763, EN ISO 22764, EN ISO 22765, EN ISO 22766, EN ISO 22767, EN ISO 22768, EN ISO 22769, EN ISO 22770, EN ISO 22771, EN ISO 22772, EN ISO 22773, EN ISO 22774, EN ISO 22775, EN ISO 22776, EN ISO 22777, EN ISO 22778, EN ISO 22779, EN ISO 22780, EN ISO 22781, EN ISO 22782, EN ISO 22783, EN ISO 22784, EN ISO 22785, EN ISO 22786, EN ISO 22787, EN ISO 22788, EN ISO 22789, EN ISO 22790, EN ISO 22791, EN ISO 22792, EN ISO 22793, EN ISO 22794, EN ISO 22795, EN ISO 22796, EN ISO 22797, EN ISO 22798, EN ISO 22799, EN ISO 22800, EN ISO 22801, EN ISO 22802, EN ISO 22803, EN ISO 22804, EN ISO 22805, EN ISO 22806, EN ISO 22807, EN ISO 22808, EN ISO 22809, EN ISO 22810, EN ISO 22811, EN ISO 22812, EN ISO 22813, EN ISO 22814, EN ISO 22815, EN ISO 22816, EN ISO 22817, EN ISO 22818, EN ISO 22819, EN ISO 22820, EN ISO 22821, EN ISO 22822, EN ISO 22823, EN ISO 22824, EN ISO 22825, EN ISO 22826, EN ISO 22827, EN ISO 22828, EN ISO 22829, EN ISO 22830, EN ISO 22831, EN ISO 22832, EN ISO 22833, EN ISO 22834, EN ISO 22835, EN ISO 22836, EN ISO 22837, EN ISO 22838, EN ISO 22839, EN ISO 22840, EN ISO 22841, EN ISO 22842, EN ISO 22843, EN ISO 22844, EN ISO 22845, EN ISO 22846, EN ISO 22847, EN ISO 22848, EN ISO 22849, EN ISO 22850, EN ISO 22851, EN ISO 22852, EN ISO 22853, EN ISO 22854, EN ISO 22855, EN ISO 22856, EN ISO 22857, EN ISO 22858, EN ISO 22859, EN ISO 22860, EN ISO 22861, EN ISO 22862, EN ISO 22863, EN ISO 22864, EN ISO 22865, EN ISO 22866, EN ISO 22867, EN ISO 22868, EN ISO 22869, EN ISO 22870, EN ISO 22871, EN ISO 22872, EN ISO 22873, EN ISO 22874, EN ISO 22875, EN ISO 22876, EN ISO 22877, EN ISO 22878, EN ISO 22879, EN ISO 22880, EN ISO 22881, EN ISO 22882, EN ISO 22883, EN ISO 22884, EN ISO 22885, EN ISO 22886, EN ISO 22887, EN ISO 22888, EN ISO 22889, EN ISO 22890, EN ISO 22891, EN ISO 22892, EN ISO 22893, EN ISO 22894, EN ISO 22895, EN ISO 22896, EN ISO 22897, EN ISO 22898, EN ISO 22899, EN ISO 22900, EN ISO 22901, EN ISO 22902, EN ISO 22903, EN ISO 22904, EN ISO 22905, EN ISO 22906, EN ISO 22907, EN ISO 22908, EN ISO 22909, EN ISO 22910, EN ISO 22911, EN ISO 22912, EN ISO 22913, EN ISO 22914, EN ISO 22915, EN ISO 22916, EN ISO 22917, EN ISO 22918, EN ISO 22919, EN ISO 22920, EN ISO 22921, EN ISO 22922, EN ISO 22923, EN ISO 22924, EN ISO 22925, EN ISO 22926, EN ISO 22927, EN ISO 22928, EN ISO 22929, EN ISO 22930, EN ISO 22931, EN ISO 22932, EN ISO 22933, EN ISO 22934, EN ISO 22935, EN ISO 22936, EN ISO 22937, EN ISO 22938, EN ISO 22939, EN ISO 22940, EN ISO 22941, EN ISO 22942, EN ISO 22943, EN ISO 22944, EN ISO 22945, EN ISO 22946, EN ISO 22947, EN ISO 22948, EN ISO 22949, EN ISO 22950, EN ISO 22951, EN ISO 22952, EN ISO 22953, EN ISO 22954, EN ISO 22955, EN ISO 22956, EN ISO 22957, EN ISO 22958, EN ISO 22959, EN ISO 22960, EN ISO 22961, EN ISO 22962, EN ISO 22963, EN ISO 22964, EN ISO 22965, EN ISO 22966, EN ISO 22967, EN ISO 22968, EN ISO 22969, EN ISO 22970, EN ISO 22971, EN ISO 22972, EN ISO 22973, EN ISO 22974, EN ISO 22975, EN ISO 22976, EN ISO 22977, EN ISO 22978, EN ISO 22979, EN ISO 22980, EN ISO 22981, EN ISO 22982, EN ISO 22983, EN ISO 22984, EN ISO 22985, EN ISO 22986, EN ISO 22987, EN ISO 22988, EN ISO 22989, EN ISO 22990, EN ISO 22991, EN ISO 22992, EN ISO 22993, EN ISO 22994, EN ISO 22995, EN ISO 22996, EN ISO 22997, EN ISO 22998, EN ISO 22999, EN ISO 23000

Ansell

Instructions for use 06/17

For more information, visit: www.ansell.com

Australia: Ansell Limited, Level 5, 270 Victoria Street, Melbourne, VIC 3000, Australia. Tel: +61 800 803 578. Fax: +61 3 9601 2371.
North America Region: Ansell Healthcare Products LLC, 11 Wood Avenue South, Suite 200, North Plainfield, NJ 07063, USA. Tel: +1 800 803 0444. Fax: +1 800 803 0445.
Europe, Middle East and Africa (EMEA) Region: Ansell Healthcare Europe NV, Riverside Business Park, Blvd International 35, 1078 Brussels, Belgium. Tel: +32 2 328 74 00. Fax: +32 2 328 74 01.
Latin America and Caribbean Region: Ansell BRL Ltda, Rua das Esmeraldas 434-47, Andar 300, São Paulo, SP 05466-900, São Paulo, Brazil. Tel: +55 11 3668 8300. Fax: +55 11 3668 8300.
Asia Pacific Region: Ansell Global Trading Center, P.O. Box 502, P.O. Box 502, P.O. Box 502, Singapore 050502, Singapore. Tel: +65 6339 0200. Fax: +65 6339 0200.
Russia: OOO Ansell PRC, 12810 Moscow, Moscow, Russian Federation. Tel: +7 495 238 11 11. Fax: +7 495 238 11 11.

INSTRUCTIONS FOR USE EN ANSELL GENERAL PURPOSE GLOVES & SLEEVES GP CAT II VERSION

INSTRUCCIONES DE USO ES GUANTES Y MANGUITOS ANSELL PARA USO GENERAL GP CAT II VERSION

ISTRUZIONI PER L'USO IT QUANTI E MANGIOTTI ANSELL PER USO GENERALE GP VERSION CAT II

GEbruiksaanwijzing NL ANSELL-HANDSCHEN EN -ARMBESCHERMERS VOOR ALGEMEEN GEBRUIK GP CAT II VERSIE

BRUGSANVISNING DA ANSELL HANDESK OG ARMBESKÆRMER TIL ALMENE BRUG GP CAT II VERSION

BRUKSANVISNING NO ANSELL HANDESK OG ARMBESKÆRMER GJENERELLE FORMÅL GP CAT II VERSION

ارشادات الاستخدام AR فائز وانسل قفازات وكمادات عامة الاستخدام GP CAT II نسخة

使用説明書 JP アンセル汎用手袋&スリーブ GP CAT IIバージョン

MODE D'EMPLOI FR GANTS ET MANCHETTES ANSELL À USAGE GÉNÉRAL VERSION GP CAT II

GEbrauchsanleitung DE MERKZURHANDSCHUNG UND ARMBESCHÜTZER VON ANSELL GP-KAT-II-VERSION

INSTRUÇÕES DE UTILIZAÇÃO PT ANSELL – LUVA E MANGÁ PARA FINS GERAIS VERSÃO GP - CAT II

ΟΔΗΓΙΕΣ ΧΡΗΣΗΣ EL ΑΝΣΕΛ ΚΑΙ ΠΕΡΙΒΛΗΤΗΣ ΑΝΣΕΛ ΓΕΝΙΚΗΣ ΧΡΗΣΗΣ ΕΚΔΟΣΗ GP ΚΑΤΗΓΟΡΙΑ II

KÄYTTÖOHJEET FI ANSELLI YLEISKÄYTTÖN TÄKÄYTTÖT KÄSIEN JA KÄSIVARUSTUKSET GP KAT II -VERSIO

BRUKSANVISNING SV ANSELLS HANDESK OCH ARMBESKÄRM FÖR ALLMÄNNA ÄNDAMÅL GP-VERSION KAT II

ИНСТРУКЦИЯ ПО ПРИМЕНЕНИЮ RU УНИВЕРСАЛЬНЫЕ ПЕРЧАТКИ И НАРУКВЯЖКИ КОМПАНИИ ANSELL ВЕРСИЯ GP -КАТЕГОРИИ II

PETUNJUK PENGGUNAAN ID SARUNG TANGAN & BAWANG LENGAN BERBAGU ANSELL VERSI GP CAT II

220mm

NAVOD NA POUIŽITÍ CS VÍCEÚČELOVÉ RUKAVICE A MANGLEVNY NA PAZE ANSELL VERZE GP KAT II

HASZNÁLATI ÚTMUTATÓ HU ANSELL ÁLTALÁNOS CÉLÚ KEZTVEKÉSI ÉS KARVEKÉSI ANSELL VERZIÓ

LIETOŠANAS INSTRUKCIJA LV ANSELL PĻAŠA PĒRĒTOŠUMA CĪMI UN PĒRUKVĒNES GP KAT II VARIANTS

INSTRUKCJE UŻYTKOWNIA PL RĘKAWICZE I MANGIANY ANSELL DO ZASTOSOWAŃ OGÓLNYCH WERSJA GP KAT II

ИНСТРУКЦИИ ЗА УПОТРЕБА BG УНИВЕРСАЛНИ РЪКВАЩИ И РЪКВАБЕЛИ ANSELL ВЕРСИЯ GP КАТ II

NAVODILA ZA UPORABO SL RUKAVICE I ROKAVI ANSELL ZA SPLOŠNO UPORABO GP RAZLIČNIH KATEGORIJE

사용 설명서 KO ANSELL 종합 용도 장갑 GP CAT II 버전

คำแนะนำ/คู่มือการใช้งาน TH ทั่วประเภทยูนิฟิเคชัน (ทั่วไป) แอนเซลล์ เวอร์ชัน GP ประเภท II

KASUTUSJUHISED ET ANSELL KINDAD JA VARRUKAD OLDEKESK OTSTARBEKES GP KAT II VERSIOON

NAUDGĀJĀMO INSTRUKCIJAS LT „ANSELL“ BENDROS PASKIRTIES PIRŠTINES RANKOVĒS GP II KAT. VERSIJA

STRUZZJONIJIET GHALL-UŻU MT INWANTI W SLEEVES ANSELL ĠRAL SKOPPIET ĠENERALI VERŻJONI GP KATEGORIJA II

INSTRUCIUNI DE UTILIZARE RO ANSELL ÎN MÂNCĂI ANSELL DE Uz GENERAL VERSIUNEA GP CAT II

NAVOD NA POUIŽIVANIE SK RUKAVICE A RUKAVKY ANSELL NA VŠEOBECNÉ UČELY VERZIA GP KAT II

KULLANIM TALIMLARI TR ANSELL GENEL AMAÇLI ELEĐNEN VE KOLLUKLARI GP CAT II SÜRÜĐU

ARAHAN UNTUK PENGGUNAAN MS SARUNG TANGAN & LENGAN PENGGUNAAN AM ANSELL VERSI GP KATEGORI II

使用说明 ZH 安塞尔用于各种场景 GP 手套版本

Ansell

Ansell

Ansell

Ansell

Ansell

Ansell

Ansell

Ansell

810mm

810mm

2006/07 15/1